



13383513

Frame 1gang, can be illuminated 230 V, for housing surface-mtd, W.1, blue

Technical characteristics

Main electrical features

Rated current	2.5 mA
---------------	--------

Dimensions

Depth	23 mm
Height	83 mm
Width	83 mm

Endurance

Service life of the LED	30000 h
-------------------------	---------

Capacity

Number of sockets	1
-------------------	---

Materials

Colour	light grey
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	thermoplastic
Surface appearance	matt
Type of surface treatment	untreated

Lighting control

Light colour	blue
--------------	------

Installation, mounting

Installation mode	with clamp/screw fastening
-------------------	----------------------------

Equipment

Lighting	for lighting and monitoring circuit
----------	-------------------------------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

Identification

Main design line	Berker W.1
------------------	------------

Instructions

