



13383513

Frame 1gang, can be illuminated 230 V, for housing surface-mtd, W.1, blue

Technical characteristics

Main electrical features

Rated current	2.5 mA
---------------	--------

Dimensions

Depth	23 mm
-------	-------

Height	83 mm
--------	-------

Width	83 mm
-------	-------

Endurance

Service life of the LED	30000 h
-------------------------	---------

Capacity

Number of sockets	1
-------------------	---

Materials

Colour	light grey
--------	------------

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Surface appearance	matt
--------------------	------

Type of surface treatment	untreated
---------------------------	-----------

Lighting control

Light colour	blue
--------------	------

Installation, mounting

Installation mode	with clamp/screw fastening
-------------------	----------------------------

Equipment

Lighting	for lighting and monitoring circuit
----------	-------------------------------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-15...30 °C
-----------------------	-------------

Storage/transport temperature	-50...50 °C
-------------------------------	-------------

Identification

Main design line	Berker W.1
------------------	------------

Instructions

