



13737009

### Frame 3gang hor., K.1, p. white glossy

#### Technical characteristics

##### Dimensions

|        |         |
|--------|---------|
| Depth  | 9.9 mm  |
| Height | 80.5 mm |
| Width  | 229 mm  |

##### Capacity

|                   |   |
|-------------------|---|
| Number of sockets | 3 |
|-------------------|---|

##### Materials

|                           |                       |
|---------------------------|-----------------------|
| Colour of design line     | polar white           |
| Colour                    | white                 |
| RAL colour                | RAL 9010 - Pure white |
| Surface appearance        | glossy                |
| Type of surface treatment | untreated             |

##### Installation, mounting

|                   |                 |
|-------------------|-----------------|
| Installation mode | clamp fastening |
|-------------------|-----------------|

##### Safety

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |
| Halogen free  | Yes |

##### Identification

|                  |            |
|------------------|------------|
| Main design line | Berker K.1 |
|------------------|------------|

##### Instructions

|                   |   |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
|-------------------|---|