



1392

## Glass cover plate 2gang TS polar white glossy

### Technical characteristics

#### Dimensions

Depth	5 mm
Screw length	25 mm
Height	160 mm
Width	86 mm

#### Materials

Colour of design line	polar white
Colour	white
RAL colour	RAL 9010 - Pure white
Surface appearance	glossy
Material / surface	glass with polar white imprint on the rear

#### Installation, mounting

Screws / screwdriver	each with 2 M3.5 x 25 mm two-hole screws in chrome, gold and stainless steel for dismantling protection ; with screwdriver
Installation mode	for vertical and horizontal mounting ; clamp fastening

#### Equipment

Subplate	with polar white plastic base
----------	-------------------------------

#### Safety

Impact strength	IK02
-----------------	------

#### Identification

Main design line	Berker TS
------------------	-----------

#### Instructions

Information text	Other components from the B.7 glass range are available, e.g. SCHUKO socket outlets. Observe scale drawings!
------------------	--