



1392

## Glass cover plate 2gang TS polar white glossy

### Technical characteristics

#### Dimensions

|              |        |
|--------------|--------|
| Depth        | 5 mm   |
| Screw length | 25 mm  |
| Height       | 160 mm |
| Width        | 86 mm  |

#### Materials

|                       |  |
|-----------------------|--|
| Colour of design line | polar white                                |
| Colour                | white                                      |
| RAL colour            | RAL 9010 - Pure white                      |
| Surface appearance    | glossy                                     |
| Material / surface    | glass with polar white imprint on the rear |

#### Installation, mounting

|                      |  |
|----------------------|--|
| Screws / screwdriver | each with 2 M3.5 x 25 mm two-hole screws in chrome, gold and stainless steel for dismantling protection ; with screwdriver |
| Installation mode    | for vertical and horizontal mounting ; clamp fastening   |

#### Equipment

|          |                               |
|----------|-------------------------------|
| Subplate | with polar white plastic base |
|----------|-------------------------------|

#### Safety

|                 |      |
|-----------------|------|
| Impact strength | IK02 |
|-----------------|------|

#### Identification

|                  |           |
|------------------|-----------|
| Main design line | Berker TS |
|------------------|-----------|

#### Instructions

|                  |  |
|------------------|--|
| Information text | Other components from the B.7 glass range are available, e.g. SCHUKO socket outlets. Observe scale drawings! |
|------------------|--|