



13940004

## Frame 5gang horizontal Arsys stainless steel

### Technical characteristics

#### Dimensions

|        |          |
|--------|----------|
| Depth  | 9.5 mm   |
| Height | 80.5 mm  |
| Width  | 364.5 mm |

#### Capacity

|                   |   |
|-------------------|---|
| Number of sockets | 5 |
|-------------------|---|

#### Materials

|                           |                             |
|---------------------------|-----------------------------|
| Colour of design line     | Stainless steel             |
| Colour                    | Stainless steel             |
| Colour                    | stainless steel optics      |
| RAL colour                | RAL 9022 - Pearl light grey |
| Material / workmanship    | metal, matt finish          |
| Material                  | stainless steel             |
| Surface appearance        | matt                        |
| Type of surface treatment | untreated                   |

#### Installation, mounting

|                   |                 |
|-------------------|-----------------|
| Installation mode | clamp fastening |
|-------------------|-----------------|

#### Safety

|                     |      |
|---------------------|------|
| Protection index IP | IP20 |
| REACH conform       | Yes  |
| RoHS conform        | Yes  |
| Halogen free        | Yes  |

#### Identification

|                  |              |
|------------------|--------------|
| Main design line | Berker Arsys |
|------------------|--------------|