



14103502

FCC soc.out. insert 8/8p shielded hinged cover surf./flushmtd,cat.6,labfield,W1

Technical characteristics

Connectivity

Outlet	with straight outlet
Plug type	for RJ11, RJ12 and RJ45 plugs

Voltage

Voltage	suitable for PoE+
---------	-------------------

Frequency

Transmission bandwidth	250 MHz
------------------------	---------

Cover, door

Hinged covers	with transparent hinged cover
---------------	-------------------------------

Materials

Surface appearance	matt
Material / surface	Housing made of die-cast zinc

Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

Connection

Type of connection	with cutting terminals
Contact	with screen contacting 360° and strain relief

Cable

Wire	flexible cable routing
------	------------------------

Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

Safety

REACH conform	Yes
RoHS conform	Yes
Protection	with self-closing dust protection cover per jack

Use conditions

Operating temperature	-40...30 °C
Storage/transport temperature	-50...50 °C

Identification

Application, usage	Communication technology
Main design line	Berker W.1