



14322089

Centre plate with installation opening Ø 22.5 mm, R.1/R.3, polar white glossy

Technical characteristics

Materials

| | |
|-----------------------|-----------------|
| Colour of labelling | 105,105,105 |
| Colour of design line | polar white |
| Material for printing | ASA polar white |
| Surface appearance | glossy |

Installation, mounting

| | |
|-----------------------|----------------------------|
| Installation aperture | according to IEC 60947-5-1 |
| Cut-out | with cut-out dia. 22.5 mm |
| Installation mode | without spreader claws |

Settings

| | |
|-------------------|----------|
| Shading parameter | R1_biały |
| Laser parameter | R1_weiß |

Equipment

| | |
|------------------------------------|-----------------------|
| Type of configuration | Laserdruck |
| Supporting plate / Supporting ring | with supporting plate |

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |

Identification

| | |
|--------------------------|--------------------------------------------------------|
| Application, usage | Security and safety systems ; Communication technology |
| Main design line | Berker R.1/R.3/R.8 |
| Secondary design line(s) | Berker R.1 ; Berker R.3 ; Berker R.8 |