



181110

Push-button, NO contact, TS, chrome glossy, brass galvanised

Technical characteristics

Architecture

Type of control unit Push button

Configuration

Switch mode Normally open contact

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 12 V

Rated voltage 12 V

Electric current

Momentary-contact current 1.5 A

Dimensions

Depth 19.7 mm

Insertion depth 13 mm

Height 22 mm

Width 22 mm

Materials

Colour of design line chrome

Colour chrome

Colour chrome optics

RAL colour RAL 9006 - White aluminium

Material / workmanship brass galvanised

Material brass

Material / surface brass, refined

Installation, mounting

Installation mode for screw fastening

Connection

Type of connection with plug-in terminals

Scope of delivery

With lamp No

Equipment

Quantity of NC contacts	1
Quantity of NO contacts	1

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-20...60 °C
-----------------------	-------------

Identification

Main design line	Berker TS
------------------	-----------

Instructions

Special note text	For connection via system interfaces to radio bus, KNX radio or KNX installations. Alternatively, can be used to control relay circuits.
-------------------	--