



18301

## RolloTec precipitation sensor house electronics grey

### Technical characteristics

#### Configuration

Pre-assembled pre-assembled, with cables

#### Main electrical features

Frequency 50/60 Hz

#### Electric current

Switching current at 250 V~ (ohmic) max. 6 A

Switching current at 30 V= (ohmic) max. 3 A

#### Dimensions

Dimensions, mounting bracket (W x H x D) 130 x 90 x 90 mm

Mast Ø max. 62 mm

#### Power

Power consumption incl. additional heating max. 4.5 W

#### Detection

Dimensions sensor (L x W x H) 82 x 60 x 57.5 mm

#### Installation, mounting

Installation mode with stainless steel mounting bracket approx. 70° ;  
with pipe clamp for mast fixing

#### Cable

Pre-assembled cables ≈ 2.9 m

#### Equipment

Heating heated

Potential-free with potential-free change-over contact

#### Safety

REACH conform Yes

RoHS conform Yes

#### Use conditions

Operating temperature -30...70 °C

#### Identification

Application, usage Blind control

Main design line Blind control