



18301

RolloTec precipitation sensor house electronics grey

Technical characteristics

Configuration

Pre-assembled pre-assembled, with cables

Main electrical features

Frequency 50/60 Hz

Electric current

Switching current at 250 V~ (ohmic) max. 6 A

Switching current at 30 V= (ohmic) max. 3 A

Dimensions

Dimensions, mounting bracket (W x H x D) 130 x 90 x 90 mm

Mast Ø max. 62 mm

Power

Power consumption incl. additional heating max. 4.5 W

Detection

Dimensions sensor (L x W x H) 82 x 60 x 57.5 mm

Installation, mounting

Installation mode with stainless steel mounting bracket approx. 70° ;
with pipe clamp for mast fixing

Cable

Pre-assembled cables ≈ 2.9 m

Equipment

Heating heated

Potential-free with potential-free change-over contact

Safety

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature -30...70 °C

Identification

Application, usage Blind control

Main design line Blind control