



20346084

Floor thermostat w. NO cont., Centre pl., rocker switch, Q.x alu velvety, lacq.

#### Technical characteristics

#### Functions

Switching with on/off switch and 2 LEDs

#### Main electrical features

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50/60 Hz

#### Electric current

Switching current	10 A
-------------------	------

#### Materials

Colour	aluminium
Material / workmanship	lacquered
Material	Plastic/metal

#### LED control

LED	with LED for heating and LED for night lowering
-----	-------------------------------------------------

#### Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

#### Connection

Sensor cable length	4 m
Type of connection	with plug-in terminals
Connection	with separate connection for night lowering

#### Settings

Floor temperature setting range	10...50 °C
Room temperature setting range	5...30 °C

#### Equipment

Night lowering	≈ 5 K
Switching temperature difference	≈ 1 K
Control	setting knob with temperature range limitation
Valve drives	e.g. for valve drives closed in de-energised state

#### Use

Differentiation characteristic 1 - Sales	with rocker switch
Differentiation characteristic 3 - Sales	external temperature sensor

**Use conditions**

Energy efficiency class

I (1%)

**Identification**

Application, usage

HVAC control

Main design line

Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s)

Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9