



20346089

**Thermostat, NO contact,Cen. plate,f. heat.,rocker switch,ext.temp.sen.,Q1/3**

**Technical characteristics**

**Functions**

Switching with on/off switch and 2 LEDs

**Main electrical features**

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50/60 Hz

**Electric current**

Switching current 10 A

**Materials**

Colour of design line polar white

**LED control**

LED with LED for heating and LED for night lowering

**Installation, mounting**

Installation mode without spreader claws

**Connection**

Sensor cable length	4 m
Type of connection	with plug-in terminals
Connection	with separate connection for night lowering

**Settings**

Floor temperature setting range	10...50 °C
Room temperature setting range	5...30 °C

**Equipment**

Night lowering	≈ 5 K
Switching temperature difference	≈ 1 K
Control	setting knob with temperature range limitation
Valve drives	e.g. for valve drives closed in de-energised state

**Use**

Differentiation characteristic 1 - Sales	with rocker switch
Differentiation characteristic 3 - Sales	external temperature sensor

**Safety**

REACH conform Yes

RoHS conform	Yes
Halogen free	No
<b>Use conditions</b>	
Energy efficiency class	I (1%)
<b>Identification</b>	
Application, usage	HVAC control
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9