



2040

## Mechanical timer, 15 min, light control

### Technical characteristics

#### Functions

Running time	15 mn
--------------	-------

#### Configuration

Switch mode	2-pole off
-------------	------------

#### Main electrical features

Rated voltage	250 V AC
---------------	----------

#### Electric current

Switching current	16 AX
-------------------	-------

#### Dimensions

Insertion depth	32.3 mm
-----------------	---------

#### Materials

Material	Plastic/metal
----------	---------------

#### Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

#### Connection

Terminal	with through terminal
Type of connection	with screw terminals

#### Settings

Setting	reset with slip-clutch
---------	------------------------

#### Use cases

Application	Light control
-------------	---------------

#### Identification

Application, usage	Light control
Main design line	Light control