



2041

## Mechanical timer, 120 min, light control

### Technical characteristics

#### Functions

Running time 120 mn

#### Configuration

Switch mode 2-pole off

#### Main electrical features

Rated voltage 250 V AC

#### Electric current

Switching current 16 AX

#### Dimensions

Insertion depth 32.3 mm

#### Installation, mounting

Installation mode without spreader claws

#### Connection

Terminal with through terminal

Type of connection with screw terminals

#### Settings

Setting reset with slip-clutch

#### Use cases

Application Light control

#### Safety

REACH conform Yes

RoHS conform Yes

#### Identification

Application, usage Light control

Main design line Light control