



260009

230 V USB charging soc. out., com-tech, p. white, matt, plastic

Technical characteristics

Connectivity

Connectors / jacks with 2 USB sockets type A

Main electrical features

Rated voltage 100...240 V

Voltage

Input voltage 100...240 V AC

Output voltage 5 V DC ($\pm 5\%$)

Electric current

Output current max. 1400 mA

Output current when operating both sockets max. 1.4 A

Output current per socket max. 1 A

Fuse

Fuse short-circuit and overload proof (electronic fuse)

Dimensions

Insertion depth 32 mm

Materials

Colour of design line polar white

RAL colour RAL 9010 - Pure white

Surface appearance matt

Connection

Conductor cross-section (rigid) 2.5

USB connections according to DIN EN 50558

Type of connection with screw terminals (double for wiring through)

Use cases

Application Communication technology

Use

Differentiation characteristic 3 - Sales with screw terminals

Safety

Protection without enhanced contact protection

Identification

Application, usage Communication technology

Main design line Modul-inserts

Instructions

Information text No data transmission possible!