



26002045

230 V USB charging soc. out., 1930/R.classic, black glossy

Technical characteristics

Connectivity

Connectors / jacks with 2 USB sockets type A

Main electrical features

Rated voltage 100...240 V

Rated current 1.4 A

Voltage

Input voltage 100...240 V AC

Output voltage 5 V DC

Electric current

Output current max. 1400 mA

Output current when operating both sockets max. 1.4 A

Output current per socket max. 1 A

Fuse

Fuse short-circuit and overload proof (electronic fuse)

Dimensions

Insertion depth 32 mm

Materials

Colour of design line black

Connection

USB connections according to DIN EN 50558

Type of connection with screw terminals (double for wiring through)

Equipment

Centre plates / central plates with centre plate Ø 58 mm

Use

Differentiation characteristic 3 - Sales with screw terminals

Safety

REACH conform Yes

RoHS conform Yes

Protection without enhanced contact protection

Identification

Instructions

Information text

No data transmission possible!