



2779

Handsender für B. IQ IR Tastsensor 3 Kanal x 8 Tasten

Technical characteristics

Compatibility

Suitable for indication element No

Controls and indicators

Button / push-button with 3 channel group buttons A, B, C, with 8 channel buttons (on/off; dimmer)

Hand remote control Yes

Window transmitter No

Connectivity

Encoding with child lock

Transmission mode Infrared

Dimensions

Length 192 mm

Height 55 mm

Width 192 mm

Length

Maximum connection distance between receiver and transmitter 10m

Reach distance

IR range ≈ 10 m

Battery

Battery service life [years] ≈ 3

Detection

IR RC5 code

Materials

Colour independent of design lines anthracite

Material thermoplastic

LED control

LED with 3 channel group LEDs (also transmission and battery status LEDs)

Equipment

Number of IR channels 24

Number of channels 28

Identification

Application, usage

KNX - operating systems

Main design line

B.IQ