



28198982

Rot. dimmer cover plate, setting knob, S.1, white glossy

Technical characteristics

Architecture

Type of control unit Rotative

Functions

Soft startup bulb-preserving soft startup

Main electrical features

Nominal voltage 230 V

Frequency 50 Hz

Voltage

Operating voltage 230 V AC

Fuse

Fuse short-circuit and overload proof (fine-wire fuse)

Dimensions

Axis dimension Ø 4 mm

Power

Loss power at full load ≈ 4 W

Materials

Colour of design line white

Colour white

Material duroplastic

Incandescent bulbs control

230 V incandescent lamps and halogen lamps 60...400 W

Installation, mounting

Installation mode with spreader claws

Connection

Type of load Resistive load

Type of connection with screw terminals

Equipment

Dimming principle phase cut-on

Switches / socket outlets with rotary on/off switch

Use

Differentiation characteristic 2 - Sales

Setting knob

Differentiation characteristic 3 - Sales

with soft-lock

Use conditions

Operating temperature

5...25 °C

Identification

Application, usage

Light control

Secondary design line(s)

Berker S.1 ; Berker B.3 ; Berker B.7