



286010

Rotary dimmer house electronics

Technical characteristics

Architecture

Type of control unit Push & rotative

Main electrical features

Nominal voltage 240 V

Frequency 50/60 Hz

Voltage

Operating voltage 230 V AC

Fuse

Fine-wire fuse T 2.5 H 250

Fuse short-circuit and overload proof (fine-wire fuse)

Dimensions

Axis dimension Ø 4 mm

Incandescent bulbs control

230 V incandescent lamps and halogen lamps 60...600 W

Installation, mounting

Installation mode with spreader claws

Connection

Type of load Resistive load

Type of connection with screw terminals

Equipment

Dimming principle phase cut-on

Switches / socket outlets with change-over pressure switch

Safety

REACH conform Yes

RoHS conform Yes

Identification

Application, usage Light control

Main design line Light control

Instructions

Information text Possible to change fuse without removing cover.