



286210

## Extension units insert for universal rot. dimmer, soft-lock, light control

### Technical characteristics

#### Architecture

Type of control unit	Push & rotative
----------------------	-----------------

#### Compatibility

Extension unit	as extension unit for universal rotary dimmer
----------------	---

### Main electrical features

Nominal voltage	230 V
Frequency	50/60 Hz

#### Voltage

Operating voltage	230 V AC
Voltage	voltage test possible without dismantling

#### Dimensions

Axis dimension Ø	4 mm
------------------	------

#### Materials

Colour	not applicable
Material	Plastic/metal

#### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

#### Connection

Type of load	universal
Type of connection	with plug-in terminals

#### Scope of delivery

Component	with incremental encoder
-----------	--------------------------

#### Equipment

Number of substations	max. 5
-----------------------	--------

#### Use

Differentiation characteristic 3 - Sales	with soft-lock
--	----------------

#### Identification

Application, usage	Light control
Release issue	2
Main design line	Light control