



286210

Extension units insert for universal rot. dimmer, soft-lock, light control

Technical characteristics

Architecture

Type of control unit Push & rotative

Compatibility

Extension unit as extension unit for universal rotary dimmer

Main electrical features

Nominal voltage 230 V

Frequency 50/60 Hz

Voltage

Operating voltage 230 V AC

Voltage voltage test possible without dismantling

Dimensions

Axis dimension \varnothing 4 mm

Materials

Colour not applicable

Material Plastic/metal

Installation, mounting

Installation mode with spreader claws

Connection

Type of load universal

Type of connection with plug-in terminals

Scope of delivery

Component with incremental encoder

Equipment

Number of substations max. 5

Use

Differentiation characteristic 3 - Sales with soft-lock

Identification

Application, usage Light control

Release issue 2

Main design line Light control