



28826084

Loudspeaker Q.x alu velvety lacquered

Technical characteristics

Configuration

Pre-assembled	confectioned, with 2-core, double-insulated, flexible cable
---------------	---

Dimensions

Insertion depth	35 mm
-----------------	-------

Frequency

Frequency response (-3 dB)	170...18000 Hz
----------------------------	----------------

Resistance

Impedance	4 Ω
-----------	------------

Materials

Colour	aluminium
RAL colour	RAL 9006 - White aluminium
Material	Mixed materials
Surface appearance	velvety

Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

Connection

Conductor cross-section (flexible)	0.5 mm ²
------------------------------------	---------------------

Cable

Pre-assembled cable	≈ 25 cm
---------------------	---------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Identification

Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9