



28826084

## Loudspeaker Q.x alu velvety lacquered

### Technical characteristics

#### Configuration

Pre-assembled confectioned, with 2-core, double-insulated, flexible cable

#### Dimensions

Insertion depth 35 mm

#### Frequency

Frequency response (-3 dB) 170...18000 Hz

#### Power

Nominal/music power handling 3/4 W

#### Resistance

Impedance 4 Ω

#### Materials

Colour of design line aluminium  
Surface appearance velvety

#### Installation, mounting

Installation mode without spreader claws

#### Connection

Conductor cross-section (flexible) 0.5 mm<sup>2</sup>

#### Cable

Pre-assembled cable ≈ 25 cm

#### Safety

REACH conform Yes  
RoHS conform Yes  
Halogen free No

#### Identification

Main design line Berker Q.1/Q.3/Q.7/Q.9  
Secondary design line(s) Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9