



28826084

Loudspeaker Q.x alu velvety lacquered

Technical characteristics

Configuration

Pre-assembled confectioned, with 2-core, double-insulated, flexible cable

Dimensions

Insertion depth 35 mm

Frequency

Frequency response (-3 dB) 170...18000 Hz

Resistance

Impedance 4 Ω

Materials

Colour aluminium

RAL colour RAL 9006 - White aluminium

Material Mixed materials

Surface appearance velvety

Installation, mounting

Installation mode without spreader claws

Connection

Conductor cross-section (flexible) 0.5 mm²

Cable

Pre-assembled cable ≈ 25 cm

Identification

Main design line Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s) Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9