



2919

## Cutoff relay RMD, extension unit outputs, blind control

### Technical characteristics

#### Compatibility

Extension unit with 2 extension unit outgoing feeders for single operation

#### Connectivity

Inputs with master input e.g. for RolloTec time switch

#### Main electrical features

Frequency 50 Hz

#### Electric current

Current consumption (operation)  $\approx 10$  mA

Switching current at  $\cos \varphi = 0.6$  max. 4 A

#### Dimensions

Depth 42 mm

Assembling height as from DIN rail 39 mm

Width of rail mounted device (RMD) 2.5 modules

Height 71 mm

Width 45 mm

#### Network configuration

Network with separate mains power supply

#### Connection

Conductor cross-section (rigid) max. 2.5 mm<sup>2</sup>

Type of connection with screw terminals

#### Equipment

Activation change-over time up/down min. 0.5 s

Decoupling required for electric motor decoupling

Motor to operate 2 shutter/blind control motors

#### Use

Differentiation characteristic 3 - Sales with extension unit outputs

#### Safety

REACH conform Yes

RoHS conform Yes

#### Identification

Application, usage Blind control

