



2919

Cutoff relay RMD, extension unit outputs, blind control

Technical characteristics

Compatibility

Extension unit with 2 extension unit outgoing feeders for single operation

Connectivity

Inputs with master input e.g. for RolloTec time switch

Main electrical features

Frequency 50 Hz

Electric current

Current consumption (operation) ≈ 10 mA

Switching current at $\cos \varphi = 0.6$ max. 4 A

Dimensions

Depth 42 mm

Assembling height as from DIN rail 39 mm

Width of rail mounted device (RMD) 2.5 modules

Height 71 mm

Width 45 mm

Network configuration

Network with separate mains power supply

Connection

Conductor cross-section (rigid) 2.5

Type of connection with screw terminals

Equipment

Activation change-over time up/down min. 0.5 s

Decoupling required for electric motor decoupling

Motor to operate 2 shutter/blind control motors

Use

Differentiation characteristic 3 - Sales with extension unit outputs

Identification

Application, usage Blind control

Main design line Blind control