



2925

RolloTec standard insert house electronics

Technical characteristics

Functions

Power reserve 0 h

Configuration

Switch mode with 2 mechanically interlocked NO contacts

Main electrical features

Frequency 50/60 Hz

Dimensions

Insertion depth 32 mm

Power

Switching capacity for max. 1 motor 1000 W

Measurement

Extension unit input without 230 V extension unit inputs

Detection

Sensor Not suitable for rain and wind sensors

Materials

Colour not applicable

Material Plastic/metal

Lighting control

Twilight setting range 0 lx

Installation, mounting

Installation mode with spreader claws

Connection

Conductor cross-section (rigid) 1.5

Type of connection with screw terminals

Safety

Protection index IP IP20

Use conditions

Operating temperature 5...35 °C

Identification

Application, usage Blind control, Radio bus - operating systems

Instructions

Information text

Recommendation: use deep box.