



2930

Cutoff relay surface-mtd/flush-mtd, blind control

Technical characteristics

Connectivity

Inputs with master input e.g. for RolloTec time switch

Main electrical features

Frequency 50/60 Hz

Electric current

Current consumption (operation) ≈ 10 mA

Switching current at $\cos \varphi = 0.6$ max. 3 A

Switching current at $\cos \varphi = 1$ max. 8 A

Dimensions

Depth 50 mm

Height 52 mm

Width 22 mm

Network configuration

Network with separate mains power supply

Connection

Type of connection with screw terminals

Accessories included

Box installation in flush-mounted or splash-protected junction box

Equipment

Activation change-over time up/down min. 0.5 s

Motor to operate 2 shutter/blind control motors

Safety

REACH conform Yes

RoHS conform Yes

temperatur

Ambient temperature 0...60 °C

Identification

Application, usage Blind control

Main design line Blind control