



2930

## Cutoff relay surface-mtd/flush-mtd, blind control

### Technical characteristics

#### Connectivity

Inputs with master input e.g. for RolloTec time switch

#### Main electrical features

Frequency 50/60 Hz

#### Electric current

Current consumption (operation)  $\approx 10$  mA

Switching current at  $\cos \varphi = 0.6$  max. 3 A

Switching current at  $\cos \varphi = 1$  max. 8 A

#### Dimensions

Depth 50 mm

Height 52 mm

Width 22 mm

#### Network configuration

Network with separate mains power supply

#### Connection

Type of connection with screw terminals

#### Accessories included

Box installation in flush-mounted or splash-protected junction box

#### Equipment

Activation change-over time up/down min. 0.5 s

Motor to operate 2 shutter/blind control motors

#### temperatur

Ambient temperature 0...60 °C

#### Identification

Application, usage Blind control

Main design line Blind control