



29511404

**LED signal light, RGB, B.7, al., matt, lacq.**

**Technical characteristics**

**Architecture**

Fixing mode flush-mounting

**Main electrical features**

Rated voltage 230 V AC

Frequency 50/60 Hz

**Power**

Power consumption at 195 ... 265 V~, 50/60 Hz - max. 2 W

**Materials**

Colour aluminium

Colour aluminium optics

RAL colour RAL 9006 - White aluminium

Material / workmanship lacquered

Material Plastic/metal

Surface appearance matt

**LED control**

Quantity LED lamps 4

**Installation, mounting**

For installation in standard wall boxes according to DIN 49073-1

**Connection**

Conductor cross-section 2.5 mm<sup>2</sup>

**Settings**

Setting Brightness modifiable via potentiometer

**Equipment**

Lighting Colour sequence can be stopped at any position via the push-button., Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button

Switches / socket outlets colour is switchable via an external switch

**Use cases**

Application Light control

**temperatur**

Ambient temperature -5...40 °C

**Identification**

---

Secondary design line(s)

Berker S.1, Berker B.3, Berker B.7

**Instructions**

---

Special note text

For consistent illumination of all pilot lamps, connect  
max. 5 devices per 10 m of cable length.