



29517006

LED signal light, RGB, K.1, ant. matt, lacq.

Technical characteristics

Main electrical features

Rated voltage	230 V AC
Frequency	50/60 Hz

Power

Power consumption	at 195 ... 265 V~, 50/60 Hz - max. 2 W
-------------------	--

Materials

Colour of design line	anthracite
Surface appearance	matt

LED control

Quantity LED lamps	4
--------------------	---

Installation, mounting

For installation in standard wall boxes	according to DIN 49073-1
---	--------------------------

Connection

Conductor cross-section	2.5 mm ²
-------------------------	---------------------

Settings

Setting	Brightness modifiable via potentiometer
---------	---

Equipment

Lighting	Colour sequence can be stopped at any position via the push-button. ; Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button
Switches / socket outlets	colour is switchable via an external switch

Use cases

Application	Light control
-------------	---------------

temperatur

Ambient temperature	-5...40 °C
---------------------	------------

Identification

Main design line	Berker K.1
------------------	------------

Instructions

Special note text	For consistent illumination of all pilot lamps, connect max. 5 devices per 10 m of cable length.
-------------------	--