



29521606

LED signal light, red/green lighting, B.3/B.7, ant., matt

Technical characteristics

Main electrical features

Rated voltage	230 V AC
Frequency	50/60 Hz

Power

Power consumption	at 230 V~, 50 Hz - per colour max. 0,5 W
-------------------	--

Materials

Colour of design line	anthracite
Surface appearance	matt

LED control

Quantity LED lamps	4
--------------------	---

Installation, mounting

For installation in standard wall boxes	according to DIN 49073-1
---	--------------------------

Connection

Conductor cross-section	2.5 mm ²
-------------------------	---------------------

Equipment

Switches / socket outlets	switchable between red and green via separate switches
---------------------------	--

Use cases

Application	Light control
-------------	---------------

Safety

REACH conform	Yes
RoHS conform	Yes

temperatur

Ambient temperature	-5...40 °C
---------------------	------------

Identification

Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7