



29521606

LED signal light, red/green lighting, B.3/B.7, ant., matt

Technical characteristics

Main electrical features

Rated voltage 230 V AC

Power

Power consumption at 230 V~, 50 Hz - per colour max. 0,5 W

Materials

Colour of design line anthracite

Surface appearance matt

LED control

Quantity LED lamps 4

Installation, mounting

For installation in standard wall boxes according to DIN 49073-1

Connection

Conductor cross-section 2.5 mm²

Equipment

Switches / socket outlets switchable between red and green via separate switches

Use cases

Application Light control

Safety

REACH conform Yes

RoHS conform Yes

temperatur

Ambient temperature -5...40 °C

Identification

Main design line Berker S.1/B.3/B.7

Secondary design line(s) Berker S.1 ; Berker B.3 ; Berker B.7