



29521606

**LED signal light, red/green lighting, B.3/B.7, ant., matt**

**Technical characteristics**

**Architecture**

Fixing mode	flush-mounting
-------------	----------------

**Main electrical features**

Rated voltage	230 V AC
Frequency	50/60 Hz

**Power**

Power consumption	at 230 V~, 50 Hz - per colour max. 0,5 W
-------------------	--

**Materials**

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material	Plastic/metal
Surface appearance	matt

**LED control**

Quantity LED lamps	4
--------------------	---

**Installation, mounting**

For installation in standard wall boxes	according to DIN 49073-1
---	--------------------------

**Connection**

Conductor cross-section	2.5 mm <sup>2</sup>
-------------------------	---------------------

**Equipment**

Switches / socket outlets	switchable between red and green via separate switches
---------------------------	--

**Use cases**

Application	Light control
-------------	---------------

**Safety**

REACH conform	Yes
RoHS conform	Yes

**temperatur**

Ambient temperature	-5...40 °C
---------------------	------------

**Identification**

Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7