



29526086

LED signal light, red/green lighting, Q.x, ant. velvety, lacq.

Technical characteristics

Architecture

Fixing mode flush-mounting

Main electrical features

Rated voltage 230 V AC

Frequency 50/60 Hz

Power

Power consumption at 230 V~, 50 Hz - per colour max. 0,5 W

Materials

Colour of design line anthracite

Colour anthracite

Colour anthracite charcoal grey

RAL colour RAL 7021 - Black grey

Material / workmanship lacquered

Material Plastic/metal

Surface appearance velvety

LED control

Quantity LED lamps 4

Installation, mounting

For installation in standard wall boxes according to DIN 49073-1

Connection

Conductor cross-section 2.5 mm²

Equipment

Switches / socket outlets switchable between red and green via separate switches

Use cases

Application Light control

temperatur

Ambient temperature -5...40 °C

Identification

Main design line Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s) Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9