



29526089

**LED signal light, red/green lighting, Q.x, p. white velvety**

**Technical characteristics**

**Architecture**

Fixing mode flush-mounting

**Main electrical features**

Rated voltage 230 V AC

Frequency 50/60 Hz

**Power**

Power consumption at 230 V~, 50 Hz - per colour max. 0,5 W

**Materials**

Colour of design line polar white

Colour polarwhite

Colour white

RAL colour RAL 9010 - Pure white

Material Plastic/metal

Surface appearance velvety

**LED control**

Quantity LED lamps 4

**Installation, mounting**

For installation in standard wall boxes according to DIN 49073-1

**Connection**

Conductor cross-section 2.5 mm<sup>2</sup>

**Equipment**

Switches / socket outlets switchable between red and green via separate switches

**Use cases**

Application Light control

**temperatur**

Ambient temperature -5...40 °C

**Identification**

Main design line Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s) Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9