



29527003

LED signal light, red/green lighting, K.5, al., matt, lacq.

Technical characteristics

Architecture

Fixing mode flush-mounting

Main electrical features

Rated voltage 230 V AC

Frequency 50/60 Hz

Power

Power consumption at 230 V~, 50 Hz - per colour max. 0,5 W

Materials

Colour aluminium

Colour aluminium optics

RAL colour RAL 9006 - White aluminium

Material / workmanship lacquered

Material Plastic/metal

Surface appearance matt

LED control

Quantity LED lamps 4

Installation, mounting

For installation in standard wall boxes according to DIN 49073-1

Connection

Conductor cross-section 2.5 mm²

Equipment

Switches / socket outlets switchable between red and green via separate switches

Use cases

Application Light control

temperatur

Ambient temperature -5...40 °C

Identification

Main design line Berker K.5