



29527004

LED signal light, red/green lighting, K.5, stainless steel matt, lacq.

Technical characteristics

Main electrical features

Rated voltage	230 V AC
Frequency	50/60 Hz

Power

Power consumption	at 230 V~, 50 Hz - per colour max. 0,5 W
-------------------	--

Materials

Colour of design line	stainless steel
Material / workmanship	lacquered
Surface appearance	matt

LED control

Quantity LED lamps	4
--------------------	---

Installation, mounting

For installation in standard wall boxes	according to DIN 49073-1
---	--------------------------

Connection

Conductor cross-section	2.5 mm ²
-------------------------	---------------------

Equipment

Switches / socket outlets	switchable between red and green via separate switches
---------------------------	--

Use cases

Application	Light control
-------------	---------------

Safety

REACH conform	Yes
RoHS conform	Yes

temperatur

Ambient temperature	-5...40 °C
---------------------	------------

Identification

Main design line	Berker K.5
------------------	------------