



29527009

## LED signal light, red/green lighting, K.1, p. white glossy

### Technical characteristics

#### Main electrical features

Rated voltage	230 V AC
Frequency	50/60 Hz

#### Power

Power consumption	at 230 V~, 50 Hz - per colour max. 0,5 W
-------------------	--

#### Materials

Colour of design line	polar white
Colour	white
RAL colour	RAL 9010 - Pure white
Surface appearance	glossy

#### LED control

Quantity LED lamps	4
--------------------	---

#### Installation, mounting

For installation in standard wall boxes	according to DIN 49073-1
---	--------------------------

#### Connection

Conductor cross-section	2.5 mm <sup>2</sup>
-------------------------	---------------------

#### Equipment

Switches / socket outlets	switchable between red and green via separate switches
---------------------------	--

#### Use cases

Application	Light control
-------------	---------------

#### Safety

REACH conform	Yes
RoHS conform	Yes

#### temperatur

Ambient temperature	-5...40 °C
---------------------	------------

#### Identification

Main design line	Berker K.1
------------------	------------