



29527009

## LED signal light, red/green lighting, K.1, p. white glossy

### Technical characteristics

#### Architecture

Fixing mode flush-mounting

#### Main electrical features

Rated voltage 230 V AC

Frequency 50/60 Hz

#### Power

Power consumption at 230 V~, 50 Hz - per colour max. 0,5 W

#### Materials

Colour of design line polar white

Colour polarwhite

Colour white

RAL colour RAL 9010 - Pure white

Material Plastic/metal

#### LED control

Quantity LED lamps 4

#### Installation, mounting

For installation in standard wall boxes according to DIN 49073-1

#### Connection

Conductor cross-section 2.5 mm<sup>2</sup>

#### Equipment

Switches / socket outlets switchable between red and green via separate switches

#### Use cases

Application Light control

#### temperatur

Ambient temperature -5...40 °C

#### Identification

Main design line Berker K.1