



29528982

## LED signal light, red/green lighting, S.1, white glossy

### Technical characteristics

#### Main electrical features

Rated voltage 230 V AC

#### Power

Power consumption at 230 V~, 50 Hz - per colour max. 0,5 W

#### Materials

Colour of design line white

Colour white

Colour white

Surface appearance glossy

#### LED control

Quantity LED lamps 4

#### Installation, mounting

For installation in standard wall boxes according to DIN 49073-1

#### Connection

Conductor cross-section 2.5 mm<sup>2</sup>

#### Equipment

Switches / socket outlets switchable between red and green via separate switches

#### Use cases

Application Light control

#### Safety

REACH conform Yes

RoHS conform Yes

#### temperatur

Ambient temperature -5...40 °C

#### Identification

Main design line Berker S.1/B.3/B.7

Secondary design line(s) Berker S.1 ; Berker B.3 ; Berker B.7