



29531404

**LED signal light, white lighting, B.7, al., matt, lacq.**

**Technical characteristics**

**Main electrical features**

Rated voltage	230 V AC
Frequency	50/60 Hz

**Power**

Power consumption	at 230 V~, 50 Hz - max. 1 W
-------------------	-----------------------------

**Materials**

Colour of design line	aluminium
Material / workmanship	lacquered
Surface appearance	matt

**LED control**

Quantity LED lamps	4
--------------------	---

**Installation, mounting**

For installation in standard wall boxes	according to DIN 49073-1
---	--------------------------

**Connection**

Conductor cross-section	2.5 mm <sup>2</sup>
-------------------------	---------------------

**Settings**

Setting	Brightness modifiable via potentiometer
---------	---

**Equipment**

Lighting	Light colour cold white
Switches / socket outlets	switchable via separate switch

**Use cases**

Application	Light control
-------------	---------------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

**temperatur**

Ambient temperature	-5...40 °C
---------------------	------------

**Identification**

Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7