



29532045

LED signal light, white lighting, R.1/R.3, black glossy

Technical characteristics

Main electrical features

Rated voltage	230 V AC
Frequency	50/60 Hz

Power

Power consumption	at 230 V~, 50 Hz - max. 1 W
-------------------	-----------------------------

Materials

Colour of design line	black
Colour	black
Surface appearance	glossy

LED control

Quantity LED lamps	4
--------------------	---

Installation, mounting

For installation in standard wall boxes	according to DIN 49073-1
---	--------------------------

Connection

Conductor cross-section	2.5 mm ²
-------------------------	---------------------

Settings

Setting	Brightness modifiable via potentiometer
---------	---

Equipment

Lighting	Light colour cold white
Switches / socket outlets	switchable via separate switch

Use cases

Application	Light control
-------------	---------------

Safety

REACH conform	Yes
RoHS conform	Yes

temperatur

Ambient temperature	-5...40 °C
---------------------	------------

Identification

Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1 ; Berker R.3 ; Serie 1930 ; Series R.classic

Instructions

Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!

Special note text