



29536086

**LED signal light, white lighting, Q.x, ant. velvety, lacq.**

#### Technical characteristics

##### Architecture

Fixing mode flush-mounting

##### Main electrical features

Rated voltage 230 V AC

Frequency 50/60 Hz

##### Power

Power consumption at 230 V~, 50 Hz - max. 1 W

##### Materials

Colour of design line anthracite

Colour charcoal

Colour anthracite charcoal grey

RAL colour RAL 7021 - Black grey

Material / workmanship lacquered

Material Plastic/metal

Surface appearance velvety

##### LED control

Quantity LED lamps 4

##### Installation, mounting

For installation in standard wall boxes according to DIN 49073-1

##### Connection

Conductor cross-section 2.5 mm<sup>2</sup>

##### Settings

Setting Brightness modifiable via potentiometer

##### Equipment

Lighting Light colour cold white

Switches / socket outlets switchable via separate switch

##### Use cases

Application Light control

##### temperatur

Ambient temperature -5...40 °C

##### Identification

