



29537003

**LED signal light, white lighting, K.5, al., matt, lacq.**

#### Technical characteristics

##### Main electrical features

Rated voltage	230 V AC
Frequency	50/60 Hz

##### Power

Power consumption	at 230 V~, 50 Hz - max. 1 W
-------------------	-----------------------------

##### Materials

Colour of design line	aluminium
Material / workmanship	lacquered
Surface appearance	matt

##### LED control

Quantity LED lamps	4
--------------------	---

##### Installation, mounting

For installation in standard wall boxes	according to DIN 49073-1
---	--------------------------

##### Connection

Conductor cross-section	2.5 mm <sup>2</sup>
-------------------------	---------------------

##### Settings

Setting	Brightness modifiable via potentiometer
---------	---

##### Equipment

Lighting	Light colour cold white
Switches / socket outlets	switchable via separate switch

##### Use cases

Application	Light control
-------------	---------------

##### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

##### temperatur

Ambient temperature	-5...40 °C
---------------------	------------

##### Identification

Main design line	Berker K.5
------------------	------------