



29537003

**LED signal light, white lighting, K.5, al., matt, lacq.**

**Technical characteristics**

**Architecture**

Fixing mode flush-mounting

**Main electrical features**

Rated voltage 230 V AC

Frequency 50/60 Hz

**Power**

Power consumption at 230 V~, 50 Hz - max. 1 W

**Materials**

Colour aluminium

Colour aluminium optics

RAL colour RAL 9006 - White aluminium

Material / workmanship lacquered

Material Plastic/metal

Surface appearance matt

**LED control**

Quantity LED lamps 4

**Installation, mounting**

For installation in standard wall boxes according to DIN 49073-1

**Connection**

Conductor cross-section 2.5 mm<sup>2</sup>

**Settings**

Setting Brightness modifiable via potentiometer

**Equipment**

Lighting Light colour cold white

Switches / socket outlets switchable via separate switch

**Use cases**

Application Light control

**temperatur**

Ambient temperature -5...40 °C

**Identification**

Main design line Berker K.5