



29537006

**LED signal light, white lighting, K.1, ant. matt, lacq.**

#### Technical characteristics

##### Architecture

Fixing mode	flush-mounting
-------------	----------------

##### Main electrical features

Rated voltage	230 V AC
Frequency	50/60 Hz

##### Power

Power consumption	at 230 V~, 50 Hz - max. 1 W
-------------------	-----------------------------

##### Materials

Colour of design line	anthracite
Colour	charcoal
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material	Plastic/metal
Surface appearance	matt

##### LED control

Quantity LED lamps	4
--------------------	---

##### Installation, mounting

For installation in standard wall boxes	according to DIN 49073-1
---	--------------------------

##### Connection

Conductor cross-section	2.5 mm <sup>2</sup>
-------------------------	---------------------

##### Settings

Setting	Brightness modifiable via potentiometer
---------	---

##### Equipment

Lighting	Light colour cold white
Switches / socket outlets	switchable via separate switch

##### Use cases

Application	Light control
-------------	---------------

##### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

**temperatur**

Ambient temperature -5...40 °C

**Identification**

Main design line Berker K.1