



29538982

## LED signal light, white lighting, S.1, white glossy

### Technical characteristics

#### Architecture

Fixing mode flush-mounting

#### Main electrical features

Rated voltage 230 V AC

Frequency 50/60 Hz

#### Power

Power consumption at 230 V~, 50 Hz - max. 1 W

#### Materials

Colour of design line white

Colour white

Colour white

RAL colour RAL 1013 - Oyster white

Material Plastic/metal

Surface appearance glossy

#### LED control

Quantity LED lamps 4

#### Installation, mounting

For installation in standard wall boxes according to DIN 49073-1

#### Connection

Conductor cross-section 2.5 mm<sup>2</sup>

#### Settings

Setting Brightness modifiable via potentiometer

#### Equipment

Lighting Light colour cold white

Switches / socket outlets switchable via separate switch

#### Use cases

Application Light control

#### temperatur

Ambient temperature -5...40 °C

#### Identification

Main design line Berker S.1/B.3/B.7

