



2975

RolloTec comfort insert house electronics

Technical characteristics

Functions

Multi-phase mode	suitable for multi-phase mode
Power reserve	0 h

Configuration

Switch mode	with 2 mechanically interlocked NO contacts
-------------	---

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Insertion depth	32.3 mm
-----------------	---------

Power

Switching capacity for max. 1 motor	1000 W
-------------------------------------	--------

Measurement

Extension unit input	with 230 V extension unit inputs for up, down and sensors
----------------------	---

Detection

Sensor	Suitable for rain and wind sensors
--------	------------------------------------

Materials

Colour	not applicable
Material	Plastic/metal

Lighting control

Twilight setting range	0 lx
------------------------	------

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Conductor cross-section (rigid)	2.5
Type of connection	with screw terminals

Use

Differentiation characteristic 3 - Sales	with extension unit inputs
--	----------------------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature

5...35 °C

Identification

Application, usage

Radio bus - operating systems, Blind control

Main design line

Blind control

Instructions

Information text

Recommendation: use deep box.